


# PS-R-CNTRL



PowerShift® Rack and Module, accommodates up to 12 modules (2 separate circuits each for a total capacity of 12 RRU's with redundancy when all 12 modules are installed), includes controller Pulsar-Ede-C2

- Reduced capital/operating expenditures
- Engineering flexibility
- Future-ready design

## Product Classification

<b>Brand</b>	PowerShift®
<b>Product Series</b>	V2
<b>Product Type</b>	Shelf

## Dimensions

<b>Depth</b>	467.36 mm   18.40 in
<b>Height</b>	133.35 mm   5.25 in
<b>Weight</b>	13.15 kg   29.00 lb
<b>Width</b>	482.60 mm   19.00 in

## General Specifications

<b>Application</b>	Mounts PowerShift® modules
<b>Color</b>	Silver metallic
<b>Package Quantity</b>	1
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	3
<b>Shelf Movement</b>	Fixed

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## Included Products

Pulsar-Edge-C2 — PowerShift® High Power Pulsar Edge Controller with C2 software (included with shelf)

# Pulsar-Edge-C2

---

PowerShift® High Power Pulsar Edge Controller with C2 software (included with shelf)



## Product Classification

<b>Brand</b>	PowerShift®
<b>Product Series</b>	V2
<b>Product Type</b>	Module

## Dimensions

<b>Depth</b>	345.44 mm   13.60 in
<b>Height</b>	41.40 mm   1.63 in
<b>Width</b>	18.29 mm   0.72 in

## Electrical Specifications

<b>Backplane Interfaces</b>	10/100 Base-T Ethernet   One Galaxy Protocol (GP) RS485 bus
<b>Electrical Safety Standard</b>	UL60950-UL/cUL with CB report
<b>Front Panel Display</b>	Interface to shelf mounted interactive display

## Environmental Specifications

<b>Ambient Temperature</b>	65 °C   -40 °C
<b>Mean Time Between Failures (MTBF)</b>	300000 h @ 25 °C
<b>Relative Humidity</b>	95%, non-condensing

## General Specifications

<b>Package Quantity</b>	1
-------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

