



PATCHMAX® BP2100 Blank Plate

Product Classification

Portfolio	SYSTIMAX®
Brand	PATCHMAX®
Product Type	Blank plate
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Electrical Specifications

ANSI/TIA Category	5e
--------------------------	----

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Color	Black
Package Quantity	1

Mechanical Specifications

Material Type	Powder-coated steel
----------------------	---------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

