



GigaSPEED X10D® XL® M2000 U/UTP Modular Panel 2U Cord Manager Kit

OBSOLETE

Product Classification

Portfolio	CommScope®
Brand	GigaSPEED X10D®
Product Type	Cable management panel
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Depth	95.25 mm 3.75 in
Height	82.55 mm 3.25 in
Width	9.53 mm 0.38 in

Electrical Specifications

ANSI/TIA Category	3 5 5e 6 6A
--------------------------	---------------------

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Color	Black
Package Quantity	5
Total Ports, quantity	48

Mechanical Specifications

Material Type	Powder-coated steel
----------------------	---------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

