

ReadyPATCH® Multimode OM4 Keyed High Density Module, 72 LC ports, yellow

## Product Classification

|                              |                          |
|------------------------------|--------------------------|
| <b>Portfolio</b>             | CommScope®               |
| <b>Brand</b>                 | LazrSPEED®   ReadyPATCH® |
| <b>Product Type</b>          | Fiber module             |
| <b>Regional Availability</b> | North America            |

## Construction Materials

|                               |                     |
|-------------------------------|---------------------|
| <b>Fiber Type</b>             | OM4, LazrSPEED® 550 |
| <b>Total Fibers, quantity</b> | 72                  |

## Dimensions

|               |                      |
|---------------|----------------------|
| <b>Depth</b>  | 114.30 mm   4.50 in  |
| <b>Height</b> | 32.51 mm   1.28 in   |
| <b>Width</b>  | 424.18 mm   16.70 in |

## Environmental Specifications

|                        |    |
|------------------------|----|
| <b>Safety Standard</b> | UL |
|------------------------|----|

## General Specifications

|                                     |          |
|-------------------------------------|----------|
| <b>Interface, front</b>             | LC       |
| <b>Total Ports, quantity, front</b> | 72       |
| <b>Interface Feature, front</b>     | Keyed    |
| <b>Color, front</b>                 | Yellow   |
| <b>Adapters, quantity, front</b>    | 36       |
| <b>Shuttered</b>                    | Yes      |
| <b>Interface, rear</b>              | MPO Male |
| <b>Adapters, quantity, rear</b>     | 6        |
| <b>Interface Feature, rear</b>      | Standard |
| <b>Color, rear</b>                  | Gray     |
| <b>Package Quantity</b>             | 1        |

## Optical Performance

|                                |         |
|--------------------------------|---------|
| <b>Insertion Loss, maximum</b> | 0.90 dB |
|--------------------------------|---------|

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU  
ISO 9001:2015

**Classification**

Compliant  
Designed, manufactured and/or distributed under this quality management system

