

ReadyPATCH® Singlemode Keyed High Density Module, 72 LC ports, green

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Brand</b>	ReadyPATCH®   TeraSPEED®
<b>Product Type</b>	Fiber module
<b>Regional Availability</b>	North America

## Construction Materials

<b>Fiber Type</b>	G.652.D and G.657.A1 , TeraSPEED®   OS2
<b>Total Fibers, quantity</b>	72

## Dimensions

<b>Depth</b>	114.30 mm   4.50 in
<b>Height</b>	32.51 mm   1.28 in
<b>Width</b>	424.18 mm   16.70 in

## Environmental Specifications

<b>Safety Standard</b>	UL
------------------------	----

## General Specifications

<b>Interface, front</b>	LC
<b>Total Ports, quantity, front</b>	72
<b>Interface Feature, front</b>	Keyed
<b>Color, front</b>	Green
<b>Adapters, quantity, front</b>	36
<b>Shuttered</b>	Yes
<b>Interface, rear</b>	MPO Male
<b>Adapters, quantity, rear</b>	6
<b>Interface Feature, rear</b>	Standard
<b>Color, rear</b>	Gray
<b>Package Quantity</b>	1

## Optical Performance

<b>Insertion Loss, maximum</b>	1.15 dB
--------------------------------	---------

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU  
ISO 9001:2015

**Classification**

Compliant  
Designed, manufactured and/or distributed under this quality management system

