

ReadyPATCH® Singlemode Keyed High Density Module, 96 LC ports, green

Product Classification

Portfolio	CommScope®
Brand	ReadyPATCH® TeraSPEED®
Product Type	Fiber module
Regional Availability	North America

Construction Materials

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
Total Fibers, quantity	96

Dimensions

Depth	114.30 mm 4.50 in
Height	32.51 mm 1.28 in
Width	424.18 mm 16.70 in

Environmental Specifications

Safety Standard	UL
------------------------	----

General Specifications

Interface, front	LC
Total Ports, quantity, front	96
Interface Feature, front	Keyed
Color, front	Green
Adapters, quantity, front	48
Shuttered	Yes
Interface, rear	MPO Male
Adapters, quantity, rear	8
Interface Feature, rear	Standard
Color, rear	Gray
Package Quantity	1

Optical Performance

Insertion Loss, maximum	1.15 dB
--------------------------------	---------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system

