



12 Modular Jacks on a 100-Pair Wiring Block, With Mounting Legs

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Block
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

<b>Depth</b>	82.55 mm   3.25 in
<b>Height</b>	91.19 mm   3.59 in
<b>Width</b>	272.29 mm   10.72 in

## Electrical Specifications

<b>ANSI/TIA Category</b>	5
--------------------------	---

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Safety Standard</b>	cUL   UL

## General Specifications

<b>Product Design</b>	110
<b>Package Quantity</b>	1

## Mechanical Specifications

<b>Conductor Gauge, solid</b>	24 AWG   26 AWG
<b>Material Type</b>	Copper alloy
<b>Plug Insertion Life, minimum</b>	200 times
<b>Wiring</b>	T568B

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

