



SYSTIMAX 360™ iPatch® G2 Multimode OM4 High Density Module, 3 pack

## Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	iPatch®   SYSTIMAX 360™
<b>Product Type</b>	Fiber module
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Construction Materials

<b>Fiber Type</b>	OM4, LazrSPEED® 550
<b>Material Type</b>	Acrylonitrile butadiene styrene (ABS)   Polycarbonate (PC)

## Dimensions

<b>Depth</b>	215.90 mm   8.50 in
<b>Height</b>	82.55 mm   3.25 in
<b>Width</b>	152.40 mm   6.00 in
<b>Weight</b>	1.13 kg   2.50 lb

## Environmental Specifications

<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Safety Standard</b>	ACMA   CE   cUL   UL
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

<b>Interface, front</b>	LC
<b>Total Ports, quantity, front</b>	144
<b>Interface Feature, front</b>	Standard
<b>Color, front</b>	Aqua
<b>Color, housing</b>	Black
<b>Intelligence Type</b>	iPatch® enabled
<b>Interface, rear</b>	MPO

<b>Adapters, quantity, rear</b>	12
<b>Interface Feature, rear</b>	Reduced footprint
<b>Color, rear</b>	Black
<b>Package Quantity</b>	3

## Optical Performance

**Insertion Loss, maximum** 0.47 dB

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

