



SYSTIMAX 360™ iPatch® G2 Multimode OM1 High Density Module, 3 pack

OBSOLETE

This product was discontinued on: March 1, 2018

Product Classification

Portfolio	SYSTIMAX®
Brand	iPatch® OptiSPEED® SYSTIMAX 360™
Product Type	Fiber module
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OM1
Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC)

Dimensions

Depth	215.90 mm 8.50 in
Height	82.55 mm 3.25 in
Width	152.40 mm 6.00 in
Weight	1.13 kg 2.50 lb

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	ACMA CE CSA UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Interface, front	LC
Total Ports, quantity, front	144
Interface Feature, front	Standard

Color, front	Beige
Color, housing	Black
Intelligence Type	iPatch® enabled
Interface, rear	MPO
Adapters, quantity, rear	12
Interface Feature, rear	Reduced footprint
Color, rear	Black
Package Quantity	3

Optical Performance

Insertion Loss, maximum 0.85 dB

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

