



Equipment Rack, 2-Post, 12 in (305 mm) Channel x 7ft (2134 mm) H - 19 in (482.6 mm) Alu (45U) 12-24 Tapped Rails, Black

Product Classification

Portfolio	CommScope®
Product Type	2 post rack
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Channel Width	12.0 in
Depth	609.60 mm 24.00 in
Dimensional Standards	EIA-310-E
Height	2133.60 mm 84.00 in
Weight	24.49 kg 54.00 lb
Width	518.16 mm 20.40 in

Environmental Specifications

Safety Standard	cUL UL
------------------------	----------

General Specifications

Rack Units	45
Color	Black
Finish	Powder-coated, textured
Includes	Forty #12-24 x 1/2 in mounting screws Instruction sheet Twelve 3/8 in split lock washers Twelve 3/8-16 hex nuts Twelve 3/8-16 UNC x 1 in hex head bolts Two extruded base angles Two extruded top angles Two vertical rack rails
Package Quantity	1
Packaging Type	Flat packed
Rack Type	EIA 19 in

Mechanical Specifications

Rail Mounting Hole	#12-24
---------------------------	--------

Material Type Aluminum
Static Load Rating 453.6 kg | 1000.0 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

