



Equipment Rack, 2-Post, 3 in (76 mm) Channel x 7ft (2134 mm) H - 19 in (482.6 mm) Alu (45U) 12-24 Tapped Rails, Black

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	2 post rack
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

<b>Channel Width</b>	3.0 in
<b>Depth</b>	381.00 mm   15.00 in
<b>Dimensional Standards</b>	EIA-310-E
<b>Height</b>	2133.60 mm   84.00 in
<b>Weight</b>	12.70 kg   28.00 lb
<b>Width</b>	518.16 mm   20.40 in

## Environmental Specifications

<b>Safety Standard</b>	cUL   UL
------------------------	----------

## General Specifications

<b>Rack Units</b>	45
<b>Color</b>	Black
<b>Finish</b>	Powder-coated, textured
<b>Includes</b>	Forty #12-24 x 1/2 in mounting screws   Instruction sheet   Twelve 3/8 in split lock washers   Twelve 3/8-16 hex nuts   Twelve 3/8-16 UNC x 1 in hex head bolts   Two extruded base angles   Two extruded top angles   Two vertical rack rails
<b>Package Quantity</b>	1
<b>Packaging Type</b>	Flat packed
<b>Rack Type</b>	EIA 19 in

## Mechanical Specifications

<b>Rail Mounting Hole</b>	#12-24
---------------------------	--------

**Material Type** Aluminum  
**Static Load Rating** 453.6 kg | 1000.0 lb

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

