



Vertical Power Distribution Strip, 125V, 15A, No Surge Protection with Circuit Breaker, Standard plug

Product Classification

Portfolio	CommScope®
Product Type	Vertical power strip
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Cable Length	3.0 m 10.0 ft
Depth	41.00 mm 1.61 in
Height	41.00 mm 1.61 in
Width	1683.00 mm 66.26 in
Weight	5.00 kg 11.02 lb

Electrical Specifications

Current	15.00 A
Overcurrent Protection	15 A
Circuit Breaker	Yes
On/Off Switch	No
Plug Standard	NEMA L5-15P, straight blade
Power Frequency	50/60 Hz
Power Rating, maximum	1.40 kW
Receptacle Standard	NEMA 5-15R
Surge Indicator	No
Surge Protection	No
Voltage	125 V

Environmental Specifications

Safety Standard	cUL UL
------------------------	----------

General Specifications

Color	Black
Finish	Powder-coated, textured
Includes	Instruction sheet Plastic bottom mounting clip Two #10-32 x 1/2 in panhead screws Two plastic top mounting clips Vertical PDU

Ordering Note Not available in Mexico
Package Quantity 1
Receptacle, quantity 20

Mechanical Specifications

Material Type Steel

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

