



Vertical Power Distribution Strip, 125V, 15A, Surge Protected, with Circuit Breaker, Standard plug

OBSOLETE

This product was discontinued on: December 31, 2014

Product Classification

Portfolio	CommScope®
Product Type	Vertical power strip
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Cable Length	3.0 m 10.0 ft
Depth	41.00 mm 1.61 in
Height	41.00 mm 1.61 in
Width	1683.00 mm 66.26 in
Weight	5.00 kg 11.02 lb

Electrical Specifications

Current	15.00 A
Overcurrent Protection	15 A
Circuit Breaker	Yes
On/Off Switch	No
Plug Standard	NEMA L5-15P, straight blade
Power Frequency	50/60 Hz
Power Rating, maximum	1.40 kW
Receptacle Standard	NEMA 5-15R
Surge Indicator	Yes
Surge Protection	Yes
Voltage	125 V

Environmental Specifications

Safety Standard cUL | UL

General Specifications

Color Black

Finish Powder-coated, textured

Includes Instruction sheet | Plastic bottom mounting clip | Two #10-32 x 1/2 in panhead screws | Two plastic top mounting clips | Vertical PDU

Ordering Note Not available in Mexico

Package Quantity 1

Receptacle, quantity 20

Mechanical Specifications

Material Type Steel

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

