



Vertical Power Distribution Strip, 125V, 15A, Surge Protected, with Circuit Breaker, Twistlock plug

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Vertical power strip
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

<b>Cable Length</b>	3.0 m   10.0 ft
<b>Depth</b>	41.00 mm   1.61 in
<b>Height</b>	41.00 mm   1.61 in
<b>Width</b>	1683.00 mm   66.26 in
<b>Weight</b>	5.00 kg   11.02 lb

## Electrical Specifications

<b>Current</b>	15.00 A
<b>Overcurrent Protection</b>	15 A
<b>Circuit Breaker</b>	Yes
<b>On/Off Switch</b>	No
<b>Plug Standard</b>	NEMA L5-15P, twistlock
<b>Power Frequency</b>	50/60 Hz
<b>Power Rating, maximum</b>	1.40 kW
<b>Receptacle Standard</b>	NEMA 5-15R
<b>Surge Indicator</b>	Yes
<b>Surge Protection</b>	Yes
<b>Voltage</b>	125 V

## Environmental Specifications

<b>Safety Standard</b>	cUL   UL
------------------------	----------

## General Specifications

<b>Color</b>	Black
<b>Finish</b>	Powder-coated, textured
<b>Includes</b>	Instruction sheet   Plastic bottom mounting clip   Two #10-32 x 1/2 in panhead screws   Two plastic top mounting clips   Vertical PDU

**Ordering Note** Not available in Mexico  
**Package Quantity** 1  
**Receptacle, quantity** 20

## Mechanical Specifications

**Material Type** Steel

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

