



G2 Singlemode Standard Module, 24 LC fibers (12 duplex ports)

OBSOLETE

This product was discontinued on: June 30, 2019

Replaced By

760206540 360DMis-24LC-SM	G2 Singlemode Standard Module, 24 LC fibers (12 duplex ports) with internal shutters
760242972 360DMiP-24LC-SM	InstaPATCH® 360 TeraSPEED® Standard Module, 24 LC fibers (12 duplex ports), Blue, iPatch Ready

Product Classification

Portfolio	CommScope®
Product Type	Fiber module
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
Total Fibers, quantity	24

Dimensions

Depth	116.84 mm 4.60 in
Height	30.48 mm 1.20 in
Width	91.44 mm 3.60 in

Environmental Specifications

Safety Standard	UL
------------------------	----

General Specifications

Interface, front	LC
Total Ports, quantity, front	24
Interface Feature, front	Standard
Color, front	Blue
Adapters, quantity, front	12

Data Module Type	Standard
Intelligence Type	iPatch® ready
Shuttered	Yes
Interface, rear	MPO Pinned
Adapters, quantity, rear	2
Interface Feature, rear	Reduced footprint
Color, rear	Gray
Package Quantity	1

Optical Performance

Insertion Loss, maximum 1.05 dB

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

