

ReadyPATCH® Multimode OM1 Keyed Module, 12 LC ports, green



- Part of the Uniprise® ReadyPATCH® Pre-terminated Fiber line

OBSOLETE

This product was discontinued on: March 1, 2018

Product Classification

Portfolio	CommScope®
Brand	OptiSPEED® ReadyPATCH®
Product Type	Fiber module
Regional Availability	North America

Construction Materials

Fiber Type	OM1
Total Fibers, quantity	12

Dimensions

Depth	127.00 mm 5.00 in
Height	27.94 mm 1.10 in
Width	129.54 mm 5.10 in

Environmental Specifications

Safety Standard	UL
------------------------	----

General Specifications

Interface, front	LC
Total Ports, quantity, front	12
Interface Feature, front	Keyed
Color, front	Green
Adapters, quantity, front	6
Shuttered	Yes
Interface, rear	MPO Male
Adapters, quantity, rear	1
Interface Feature, rear	Standard

Color, rear Gray
Package Quantity 1

Optical Performance

Insertion Loss, maximum 0.90 dB

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

460117401 (Product Component—not orderable) — LazrSPEED® LC Duplex Hybrid Keyed Adapter, Green

LazrSPEED® LC Duplex Hybrid Keyed Adapter, Green

Product Classification

Portfolio	CommScope®
Brand	LazrSPEED®
Product Type	Fiber adapter
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Alignment Sleeve Material	Zirconia
Fiber Mode	Multimode Singlemode

General Specifications

Interface	LC
Body Style	Duplex
Interface Feature	Keyed
Color	Green
Package Quantity	1
Shuttered	No
Total Ports, quantity	2
Transmission Standards	TIA/EIA-568-B.3 TIA/EIA-604 FOCIS-3

Mechanical Specifications

Mount Type	No flange
-------------------	-----------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

