

ReadyPATCH® Singlemode Keyed Module, 12 LC ports, violet

- Part of the Uniprise® ReadyPATCH® Pre-terminated Fiber line



Product Classification

Portfolio	CommScope®
Brand	ReadyPATCH® TeraSPEED®
Product Type	Fiber module
Regional Availability	North America

Construction Materials

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
Total Fibers, quantity	12

Dimensions

Depth	127.00 mm 5.00 in
Height	27.94 mm 1.10 in
Width	129.54 mm 5.10 in

Environmental Specifications

Safety Standard	UL
------------------------	----

General Specifications

Interface, front	LC
Total Ports, quantity, front	12
Interface Feature, front	Keyed
Color, front	Violet
Adapters, quantity, front	6
Shuttered	Yes
Interface, rear	MPO Male
Adapters, quantity, rear	1
Interface Feature, rear	Standard
Color, rear	Gray
Package Quantity	1

Optical Performance

Insertion Loss, maximum 1.15 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system



Included Products

460117476 (Product Component—not orderable) — LazrSPEED® LC Duplex Hybrid Keyed Adapter, Violet