



ReadyPATCH® Singlemode Keyed Module, 24 LC ports, rose

- Part of the Uniprise® ReadyPATCH® Pre-terminated Fiber line

Product Classification

Portfolio	CommScope®
Brand	ReadyPATCH® TeraSPEED®
Product Type	Fiber module
Regional Availability	North America

Construction Materials

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
Total Fibers, quantity	24

Dimensions

Depth	127.00 mm 5.00 in
Height	27.94 mm 1.10 in
Width	129.54 mm 5.10 in

Environmental Specifications

Safety Standard	UL
------------------------	----

General Specifications

Interface, front	LC
Total Ports, quantity, front	24
Interface Feature, front	Keyed
Color, front	Rose
Adapters, quantity, front	12
Shuttered	Yes
Interface, rear	MPO Male
Adapters, quantity, rear	2
Interface Feature, rear	Standard
Color, rear	Gray
Package Quantity	1

Optical Performance

Insertion Loss, maximum 1.15 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system



Included Products

460117443 (Product Component—not orderable) — LazrSPEED® LC Duplex Hybrid Keyed Adapter, Rose

LazrSPEED® LC Duplex Hybrid Keyed Adapter, Rose

Product Classification

Portfolio	CommScope®
Brand	LazrSPEED®
Product Type	Fiber adapter
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Alignment Sleeve Material	Zirconia
Fiber Mode	Multimode Singlemode

General Specifications

Interface	LC
Body Style	Duplex
Interface Feature	Keyed
Color	Rose
Package Quantity	1
Shuttered	No
Total Ports, quantity	2
Transmission Standards	TIA/EIA-568-B.3 TIA/EIA-604 FOCIS-3

Mechanical Specifications

Mount Type	No flange
-------------------	-----------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

