

Wall Mount Building Entrance, top/bottom entry, up to 1728 splicing

**Replaced By**

760183681  
WBE-FXS-EMT/18T

Wall Mount Building Entrance, universal entry, up to 864 single fusion splices

## Product Classification

<b>Portfolio</b>	Uniprise®
<b>Product Type</b>	Fiber wall box
<b>Regional Availability</b>	North America

## Construction Materials

<b>Material Type</b>	Steel
----------------------	-------

## Dimensions

<b>Depth</b>	318.77 mm   12.55 in
<b>Height</b>	1066.80 mm   42.00 in
<b>Width</b>	762.00 mm   30.00 in
<b>Weight</b>	78.02 kg   172.00 lb

## Environmental Specifications

<b>Environmental Space</b>	Indoor
----------------------------	--------

## General Specifications

<b>Application</b>	Accepts up to thirty-six mass, single, or mechanical fusion splice trays
<b>Color</b>	Gray

## Mechanical Specifications

<b>Cable Entry Location</b>	Bottom   Top
<b>Cable Entry, quantity, maximum, bottom</b>	6
<b>Cable Entry, quantity, maximum, left</b>	0
<b>Cable Entry, quantity, maximum, right</b>	0
<b>Cable Entry, quantity, maximum, top</b>	6
<b>Mount Type</b>	Wall

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU  
ISO 9001:2015

**Classification**

Compliant  
Designed, manufactured and/or distributed under this quality management system

