



Wall Mount Building Entrance for Terminations and Splices, uses 4 RFE/4U panels

Product Classification

Portfolio	Uniprise®
Product Type	Fiber wall box
Regional Availability	North America

Construction Materials

Material Type	Steel
----------------------	-------

Dimensions

Depth	133.35 mm 5.25 in
Height	320.04 mm 12.60 in
Width	431.80 mm 17.00 in
Weight	10.89 kg 24.00 lb

Environmental Specifications

Environmental Space	Indoor Outdoor
----------------------------	------------------

General Specifications

Application	Accepts four PNL-type adapter panels Accepts Splice Wallet with splice trays
Color	Gray

Mechanical Specifications

Cable Entry Location	Bottom Top
Cable Entry, quantity, maximum, bottom	2
Cable Entry, quantity, maximum, left	1
Cable Entry, quantity, maximum, right	1
Cable Entry, quantity, maximum, top	2
Mount Type	Wall

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

RoHS 2011/65/EU
ISO 9001:2015

Compliant
Designed, manufactured and/or distributed under this quality management system

