

InstaPATCH® 360 SinglemodeTS TAP Module, 50:50, 12 LC ports



Product Classification

Portfolio	SYSTIMAX®
Brand	InstaPATCH® 360
Product Type	Fiber module
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	G.652.D and G.657.A1 OS2
Total Fibers, quantity	12

Dimensions

Depth	165.10 mm 6.50 in
Height	27.94 mm 1.10 in
Width	91.44 mm 3.60 in

Environmental Specifications

Safety Standard	UL
------------------------	----

General Specifications

Interface, front	LC
Total Ports, quantity, front	12
Interface Feature, front	Standard
Color, front	Blue
Adapters, quantity, front	12
Data Module Type	TAP (Traffic Access Point)
Intelligence Type	iPatch® ready
Shuttered	No
Interface, rear	MPO Male
Adapters, quantity, rear	2
Interface Feature, rear	Reduced footprint
Color, rear	Gray Red
Package Quantity	1

Optical Performance

Insertion Loss, maximum 4.27 dB

Tap Insertion Loss, maximum 4.64 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

