

G2 Singlemode APC Module, 24 LC fibers (12 duplex ports) with internal shutters



## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber module
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Construction Materials

<b>Fiber Type</b>	G.652.D and G.657.A1 , TeraSPEED®   OS2
<b>Total Fibers, quantity</b>	24

## Dimensions

<b>Depth</b>	116.84 mm   4.60 in
<b>Height</b>	27.94 mm   1.10 in
<b>Width</b>	91.44 mm   3.60 in

## Environmental Specifications

<b>Qualification Standards</b>	TIA/EIA-568-C.3
<b>Safety Standard</b>	cUL   UL

## General Specifications

<b>Interface, front</b>	LC
<b>Total Ports, quantity, front</b>	24
<b>Interface Feature, front</b>	Standard
<b>Color, front</b>	Green
<b>Interface, rear</b>	MPO Pinned
<b>Adapters, quantity, rear</b>	2
<b>Interface Feature, rear</b>	Standard
<b>Color, rear</b>	Gray
<b>Package Quantity</b>	1

## Optical Performance

<b>Insertion Loss, maximum</b>	1.05 dB
<b>Return Loss, minimum</b>	62.0 dB

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU  
ISO 9001:2015

### Classification

Compliant  
Designed, manufactured and/or distributed under this quality management system

