

FOWB Fiber Optic Wall Box, empty for holding up to 12 adapters



## Product Classification

<b>Product Type</b>	Fiber wall box
<b>Product Series</b>	FOWB
<b>Regional Availability</b>	EMEA

## General Specifications

<b>Adapters, quantity</b>	0
<b>Color</b>	Light gray
<b>Package, quantity</b>	1
<b>Splicing Capacity, maximum</b>	24

## Dimensions

<b>Depth</b>	35.00 mm   1.38 in
<b>Height</b>	220.00 mm   8.66 in
<b>Width</b>	140.00 mm   5.51 in

## Dimension Drawing

<b>Dimension Drawing</b>	Used as an image placeholder
--------------------------	------------------------------

## Mechanical Specifications

<b>Material Type</b>	Thermoplastic
<b>Mount Type</b>	Wall

## Environmental Specifications

<b>Environmental Space</b>	Indoor
<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	-25 °C to +70 °C (-13 °F to +158 °F)

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

