

FOWB Fiber Optic Wall Box, 8 singlemode SC/UPC adapters with pigtails



Product Classification

Product Type	Fiber wall box
Product Series	FOWB
Regional Availability	EMEA

General Specifications

Adapters, quantity	8
Cable Type	Pigtails - Stranded
Color	Light gray
Interface Feature, input	Standard
Interface, input	SC
Package, quantity	1
Port, quantity	8
Splicing Capacity, maximum	24

Dimensions

Depth	35.00 mm 1.38 in
Height	220.00 mm 8.66 in
Width	140.00 mm 5.51 in

Dimension Drawing

Dimension Drawing	Used as an image placeholder
--------------------------	------------------------------

Mechanical Specifications

Material Type	Thermoplastic
Mount Type	Wall

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor
Flammability Rating UL 94 V-0
Operating Temperature -25 °C to +70 °C (-13 °F to +158 °F)

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant



Included Products

CZ8468-000 | FOWB-T-NNNNN — FOWB Fiber Optic Wall Box, empty for holding up to 12 adapters

FOWB Fiber Optic Wall Box, empty for holding up to 12 adapters



Product Classification

Product Type	Fiber wall box
Product Series	FOWB
Regional Availability	EMEA

General Specifications

Adapters, quantity	0
Color	Light gray
Package, quantity	1
Splicing Capacity, maximum	24

Dimensions

Depth	35.00 mm 1.38 in
Height	220.00 mm 8.66 in
Width	140.00 mm 5.51 in

Dimension Drawing

Dimension Drawing	Used as an image placeholder
--------------------------	------------------------------

Mechanical Specifications

Material Type	Thermoplastic
Mount Type	Wall

Environmental Specifications

Environmental Space	Indoor
Flammability Rating	UL 94 V-0
Operating Temperature	-25 °C to +70 °C (-13 °F to +158 °F)

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

