



Highband® 12-module Kit, category 6A, 20-pair modules

Product Classification

Brand	Highband®
Product Series	Highband
Product Type	Back mount frame kit
Regional Availability	Australia/New Zealand

Electrical Specifications

ANSI/TIA Category	6A
Current Rating, maximum	2.50 A
Insulation Resistance, minimum	50 MOhm
Safety Voltage Rating	150 Vac
Transmission Standard	IEEE 802.3an TIA/EIA-568 Cat 6A

Environmental Specifications

Environmental Space	Indoor Outdoor
Flammability Rating	UL 94 V-0
Safety Standard	UL 1863

General Specifications

Mount Type	Backmount frames
Pairs, quantity	240
Includes	Label holder Rear cable management
Modules, quantity	12
Package Quantity	1
Packaging Type	Box Carton

Mechanical Specifications

Conductor Gauge, solid	26–22 AWG
Conductor Gauge, stranded	26–22 AWG

Contact Plating Material	Silver
Plug Insertion Life, minimum	750 times
Termination Punchdowns, minimum	200 times
Termination Tool	LSA-PLUS Punchdown tool
Termination Type	IDC

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

