

Fiber Optic Module, SM, 12 fiber, 12 LC/UPC adapters, SM fiber, angle right

Product Classification

| | |
|------------------------------|------------------------------|
| Portfolio | NETCONNECT® |
| Product Type | Fiber module |
| Regional Availability | Australia/New Zealand EMEA |

Construction Materials

| | |
|-------------------|------------|
| Fiber Type | OS2 |
| Fiber Mode | Singlemode |

Dimensions

| | |
|---------------|---------------------|
| Depth | 114.30 mm 4.50 in |
| Height | 28.96 mm 1.14 in |
| Width | 129.54 mm 5.10 in |

General Specifications

| | |
|-------------------------------------|-------------------------------|
| Interface, front | LC |
| Total Ports, quantity, front | 12 |
| Interface Feature, front | Standard |
| Color, front | Black |
| Adapter Color | Blue |
| Adapters, quantity, front | 6 |
| Body Style | Duplex Straight orientation |
| Color, housing | Black |
| Packaging Type | Bag Carton |
| Polarity | Pairs, flipped |
| Interface, rear | MPO |
| Interface Feature, rear | Standard |
| Color, rear | Black |
| Package Quantity | 1 |

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

