

FOWB Fiber Optic Wall Box, 2 singlemode SC/APC adapters with pigtails



Product Classification

Product Type	Fiber wall box
Product Series	FOWB
Regional Availability	EMEA

General Specifications

Adapters, quantity	2
Cable Type	Pigtails - Stranded
Color	Light gray
Interface Feature, input	APC
Interface, input	SC
Package, quantity	1
Port, quantity	2
Splicing Capacity, maximum	24

Dimensions

Depth	35.00 mm 1.38 in
Height	220.00 mm 8.66 in
Width	140.00 mm 5.51 in

Dimension Drawing

Dimension Drawing	Used as an image placeholder
--------------------------	------------------------------

Mechanical Specifications

Material Type	Thermoplastic
Mount Type	Wall

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor
Flammability Rating UL 94 V-0
Operating Temperature -25 °C to +70 °C (-13 °F to +158 °F)

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant



Included Products

CZ8468-000 | FOWB-T-NNNNN — FOWB Fiber Optic Wall Box, empty for holding up to 12 adapters