



## High-Density Front-Loading Cable Manager, 15U

- Offers bend radius and mechanical protection
- Suitable for Twisted Pair and Fiber Optic patch cords
- Rubber entry/exit retainers ensure cable captivity preventing accidental disturbance of patch cords

### Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Cable management hardware
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

### Dimensions

<b>Depth</b>	150.00 mm   5.91 in
<b>Height</b>	666.75 mm   26.25 in
<b>Width</b>	62.50 mm   2.46 in

### Environmental Specifications

<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Safety Standard</b>	cUL   UL

### General Specifications

<b>Color</b>	Black
<b>Rack Units</b>	15
<b>Finish</b>	Smooth
<b>Minimum Order Quantity</b>	2
<b>Ordering Note</b>	Sold per piece with an MOQ of 2 pieces
<b>Package Quantity</b>	1

### Mechanical Specifications

<b>Material Type</b>	Galvanized steel   PA   TPE
----------------------	-----------------------------

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant

