



MPOptimate® Universal Connectivity Platform (UCP) Q-Fit Module,
MPO/LC, OM4, 24F, pair flipped

This product will be discontinued on: June 28, 2019

Replaced By

760242502 G2 MPOptimate® Multimode OM4 MPO-24 Distribution Module, 1x24F MPO pinned to 24F LC Aqua,
DM24-24LC-LS-AF Method A Pair Flipped

Product Classification

Portfolio	NETCONNECT®
Brand	MPOptimate®
Product Type	Fiber module
Regional Availability	Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OM4
Fiber Mode	Multimode

General Specifications

Interface, front	LC
Total Ports, quantity, front	24
Interface Feature, front	Standard
Color, front	Black
Adapter Color	Aqua
Adapters, quantity, front	6
Application	For use with Universal Connectivity Product (UCP) panels
Body Style	Quad Straight orientation
Color, housing	Black
Packaging Type	Bag Carton
Polarity	Pairs, flipped
Interface, rear	MPO
Adapters, quantity, rear	1
Interface Feature, rear	Standard
Color, rear	Black

Package Quantity 1

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

