

ProPatch® Lite Bantam Panel, 2 x 48 bantam jacks with solder lugs, loaded with 96 PJ839 jacks

## Product Classification

<b>Brand</b>	Pro Patch®
<b>Product Series</b>	ProPatch
<b>Product Type</b>	Audio patch panel
<b>Regional Availability</b>	EMEA   Latin America   North America

## Dimensions

<b>Height</b>	44.50 mm   1.75 in
<b>Width</b>	482.60 mm   19.00 in

## Environmental Specifications

<b>Environmental Standard</b>	MIL-STD-202
<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	-40 °C to +65 °C (-40 °F to +149 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Storage Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)

## General Specifications

<b>Total Ports, quantity</b>	96
<b>Application</b>	For use with Bantam audio patch cords
<b>Growth Configuration</b>	Fully loaded
<b>Interface, front</b>	Bantam jack
<b>Mount Type</b>	Rack, horizontally oriented
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1.0

## Mechanical Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel
<b>Plug Insertion Force, maximum</b>	7 lbf
<b>Plug Insertion Life, minimum</b>	20000 times
<b>Plug Retention Force, minimum</b>	7 N   2 lbf
<b>Termination Type</b>	Solder lugs
<b>Wiring</b>	Non normalled

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

