

ProPatch® Economical Midsize Monitoring Panels, 2 RU, MVJ-3T terminated, 3 x 32, black

## Product Classification

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Brand</b>                 | Pro Patch®                           |
| <b>Product Series</b>        | ProPatch                             |
| <b>Product Type</b>          | Video patch panel                    |
| <b>Regional Availability</b> | EMEA   Latin America   North America |

## Dimensions

|               |                      |
|---------------|----------------------|
| <b>Height</b> | 44.45 mm   1.75 in   |
| <b>Width</b>  | 482.60 mm   19.00 in |

## Electrical Specifications

|                                 |        |
|---------------------------------|--------|
| <b>Characteristic Impedance</b> | 75 ohm |
|---------------------------------|--------|

## Environmental Specifications

|                               |                                      |
|-------------------------------|--------------------------------------|
| <b>Environmental Standard</b> | MIL-STD-202                          |
| <b>Flammability Rating</b>    | UL 94 V-0                            |
| <b>Operating Temperature</b>  | -40 °C to +65 °C (-40 °F to +149 °F) |
| <b>Relative Humidity</b>      | Up to 95%, non-condensing            |
| <b>Storage Temperature</b>    | -55 °C to +85 °C (-67 °F to +185 °F) |

## General Specifications

|                              |  |
|------------------------------|--|
| <b>Total Ports, quantity</b> | 64   |
| <b>Application</b>           | For use with WECO HD midsize video patch cords |
| <b>Color</b>                 | Black  |
| <b>Growth Configuration</b>  | Fully loaded                                   |
| <b>Includes</b>              | Designation strips                             |
| <b>Interface, front</b>      | MVJ-3T jack                                    |
| <b>Interface, rear</b>       | BNC female adapter                             |
| <b>Mount Type</b>            | Rack, horizontally oriented                    |
| <b>Rack Type</b>             | EIA 19 in                                      |
| <b>Rack Units</b>            | 2.0  |

## Mechanical Specifications

|                                      |               |
|--------------------------------------|---------------|
| <b>Finish</b>                        | Powder coated |
| <b>Material Type</b>                 | Steel         |
| <b>Plug Insertion Force, maximum</b> | 7 N           |

**Plug Insertion Life, minimum** 20000 times

**Plug Retention Force, minimum** 1 N | 0 lbf

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

