

ProPatch® Integrated Standard Size Video Panel, 2 RU, 3 x 26

## Product Classification

<b>Brand</b>	Pro Patch®
<b>Product Series</b>	ProPatch
<b>Product Type</b>	Video patch panel
<b>Regional Availability</b>	EMEA   Latin America   North America

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.60 mm   19.00 in

## Electrical Specifications

<b>Characteristic Impedance</b>	75 ohm
---------------------------------	--------

## Environmental Specifications

<b>Environmental Standard</b>	MIL-STD-202
<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	-40 °C to +65 °C (-40 °F to +149 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Storage Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)

## General Specifications

<b>Total Ports, quantity</b>	78
<b>Application</b>	For use with WECO HD standard size video patch cords
<b>Color</b>	Black
<b>Growth Configuration</b>	Fully loaded
<b>Includes</b>	Designation strips
<b>Interface, front</b>	SVJ-2 jack
<b>Interface, rear</b>	BNC female adapter
<b>Mount Type</b>	Rack, horizontally oriented
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	2.0

## Mechanical Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel
<b>Plug Insertion Force, maximum</b>	12 N

**Plug Insertion Life, minimum** 20000 times

**Plug Retention Force, minimum** 3 N | 1 lbf

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

