



FDH 3000 Small Fiber Distribution Pole Mount Cabinet, 144F, SC/APC, no splitters, dielectric loose tube, 100 ft, 12F

## Product Classification

<b>Product Type</b>	Fiber distribution hub
<b>Regional Availability</b>	North America
<b>Product Series</b>	FDH 3000

## General Specifications

<b>Distribution Ports, quantity</b>	288
<b>Splitter Slots, quantity</b>	12
<b>Cable Type</b>	Dielectric - Loose Tube
<b>Color</b>	Putty white
<b>Distribution Cables, quantity</b>	1
<b>Fibers per Distribution Cable, quantity</b>	144
<b>Fibers per Feeder Cable, quantity</b>	12
<b>Interface Feature, input</b>	APC
<b>Interface, input</b>	SC
<b>Package, quantity</b>	1
<b>Packaging Type</b>	Pallet

## Dimensions

<b>Enclosure Size</b>	Small
<b>Cable Length</b>	30.48 m   100.00 ft
<b>Depth</b>	457.20 mm   18.00 in
<b>Height</b>	914.40 mm   36.00 in
<b>Width</b>	685.80 mm   27.00 in

## Mechanical Specifications

<b>Mount Type</b>	Pad
<b>Access</b>	Front
<b>Finish</b>	Powder coated

**Material Type** Steel

## Environmental Specifications

**Environmental Space** Above ground

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

