



FDH 3000 Small Fiber Distribution Pole Mount Cabinet, 288F, SC/APC, no splitters, dielectric ribbon, 100 ft, 24F

Product Classification

Product Type	Fiber distribution hub
Regional Availability	North America
Product Series	FDH 3000

General Specifications

Distribution Ports, quantity	288
Splitter Slots, quantity	12
Cable Type	Armored - Single Loose Tube
Color	Putty white
Distribution Cables, quantity	1
Fibers per Distribution Cable, quantity	288
Fibers per Feeder Cable, quantity	24
Interface Feature, input	APC
Interface, input	SC
Package, quantity	1
Packaging Type	Pallet

Dimensions

Enclosure Size	Small
Cable Length	30.48 m 100.00 ft
Depth	457.00 mm 17.99 in
Height	762.00 mm 30.00 in
Width	686.00 mm 27.01 in

Mechanical Specifications

Mount Type	Pole
Access	Front
Finish	Powder coated

Material Type Steel

Environmental Specifications

Environmental Space Aerial

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

