

1671130-8

Fiber Optic Panel, 1U, 19 in, partially loaded with 12 LC/UPC MM duplex adapters, gray

Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber patch panel
Regional Availability	Australia/New Zealand EMEA

Construction Materials

Fiber Mode	Multimode
Finish	Powder coated
Material Type	Aluminum

Dimensions

Height	44.45 mm 1.75 in
Width	482.60 mm 19.00 in

General Specifications

Rack Units	1.0
Body Style	Symmetrical
Color	Gray
Color, front	Gray
Includes	Mounting hardware
Interface Feature, front	Standard
Interface, front	LC
Package Quantity	1
Rack Type	EIA 19 in
Splice Trays Included, quantity	1
Total Ports, quantity	12

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

