

Fiber Optic Module, SM, 12 fiber, 12 LC/UPC adapters, SM fiber, angle right, orange

Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber module
Regional Availability	Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OM3
Fiber Mode	Multimode

Dimensions

Depth	114.30 mm 4.50 in
Height	28.96 mm 1.14 in
Width	129.54 mm 5.10 in

General Specifications

Interface, front	LC
Total Ports, quantity, front	12
Interface Feature, front	Standard
Color, front	Black
Adapter Color	Orange
Adapters, quantity, front	6
Body Style	Duplex Straight orientation
Color, housing	Black
Packaging Type	Bag Carton
Polarity	Pairs, flipped
Interface, rear	MPO
Interface Feature, rear	Standard
Color, rear	Black
Package Quantity	1

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

