



Fiber Optic Panel, 1U, 19 in, partially loaded with 12 blue LC/UPC SM duplex adapters, black

Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber patch panel
Regional Availability	EMEA

Construction Materials

Fiber Mode	Singlemode
Finish	Powder coated
Material Type	Aluminum

Dimensions

Height	44.45 mm 1.75 in
Width	482.60 mm 19.00 in

General Specifications

Rack Units	1.0
Body Style	Symmetrical
Color	Black
Color, front	Black
Growth Configuration	Partially loaded
Includes	Mounting hardware
Interface Feature, front	Standard
Interface, front	LC
Package Quantity	1
Rack Type	EIA 19 in
Total Ports, quantity	24

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

