



Fiber Optic Module, OM4, 24 fiber, 6 quad LC/UPC adapters

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Fiber module
<b>Regional Availability</b>	North America

## Construction Materials

<b>Fiber Type</b>	OM4
<b>Fiber Mode</b>	Multimode

## General Specifications

<b>Interface, front</b>	LC
<b>Total Ports, quantity, front</b>	24
<b>Interface Feature, front</b>	Standard
<b>Color, front</b>	Black
<b>Adapters, quantity, front</b>	12
<b>Body Style</b>	Duplex   Straight orientation
<b>Color, housing</b>	Black
<b>Packaging Type</b>	Bag   Carton
<b>Interface, rear</b>	MPO
<b>Adapters, quantity, rear</b>	1
<b>Interface Feature, rear</b>	Standard
<b>Color, rear</b>	Black
<b>Package Quantity</b>	1

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

