



IFDB Fiber Optic Wall Box with Universal splice holder for up to 24 mechanical or SMOUV splices

- Allows splicing those fibers from an indoor riser cable to the individual drops
- Allows fibers from certain riser cables to be broken out without interrupting the strength member
- Separate storage of un-connected fibers from spliced drop fibers
- Compatible with mechanical, SMOUV and ANT splice protectors
- In-line and butt configuration possible for main riser cable

Product Classification

Product Type	Fiber wall box
Product Series	IFDB
Regional Availability	EMEA

General Specifications

Adapters, quantity	0
Color	Light gray
Functionality	Splicing
Package, quantity	1
Packaging Type	Bag Carton
Splice Tray Chip Type	Mechanical SMOUV
Splicing Capacity, maximum	24

Dimensions

Depth	50.00 mm 1.97 in
Height	200.00 mm 7.87 in
Width	126.00 mm 4.96 in

Dimension Drawing

Dimension Drawing	Used as an image placeholder
--------------------------	------------------------------

Mechanical Specifications

Front Cover Type	Screw-on
Material Type	Thermoplastic
Mount Type	Wall Floor

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Flammability Rating UL 94 V-0
Qualification Standard IEC 60529, IP30

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

