

# MX6-BSPL-1440-D7

OMX® Splice Cabinet, up to 1440 fiber splices, exit down, black



## Product Classification

<b>Brand</b>	OMX600®
<b>Product Series</b>	OMX
<b>Product Type</b>	Fiber entrance cabinet
<b>Regional Availability</b>	Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

<b>Depth</b>	300.00 mm   11.81 in
<b>Height</b>	2134.00 mm   84.02 in
<b>Width</b>	600.00 mm   23.62 in

## Environmental Specifications

<b>Environmental Space</b>	Indoor
----------------------------	--------

## General Specifications

<b>Color</b>	Black
<b>Splice Trays Included, quantity</b>	0
<b>Splicing Capacity Note</b>	up to 5184 ribbon fibers
<b>Splicing Capacity, maximum</b>	5184

## Mechanical Specifications

<b>Access</b>	Front
<b>Cable Entry Location</b>	Bottom
<b>Cable Exit Location</b>	Bottom
<b>Mount Type</b>	Raised floor

## Regulatory Compliance/Certifications

<b>Agency</b>	RoHS 2011/65/EU
---------------	-----------------

## Classification

