

MX6-BSPL-1440-U7



OMX® Splice Cabinet, up to 1440 fiber splices, overhead bay, enters from above, exit up

Product Classification

Brand	OMX600®
Product Series	OMX
Product Type	Fiber entrance cabinet
Regional Availability	Australia/New Zealand EMEA Latin America North America

Dimensions

Depth	300.00 mm 11.81 in
Height	2134.00 mm 84.02 in
Width	600.00 mm 23.62 in

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

General Specifications

Color	Black
Splice Trays Included, quantity	0
Splicing Capacity Note	up to 5184 ribbon fibers
Splicing Capacity, maximum	5184

Mechanical Specifications

Access	Front
Cable Entry Location	Top
Cable Exit Location	Top
Mount Type	Concrete floor

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU
---------------	-----------------

Classification

