



FMT MicroVAM Fiber Optic Module, CWDM, 4 channels, mux/demux, SC/APC, starting wavelength 1611 nm, 1310 nm upgrade port

## Product Classification

<b>Product Type</b>	CWDM module
<b>Product Series</b>	FMT
<b>Regional Availability</b>	North America

## General Specifications

<b>Distribution Type</b>	4-channel CWDM
<b>Interface, input</b>	LC
<b>Interface, output</b>	LC
<b>Application</b>	For use with FMT panels   For use with NGF frames
<b>Circuits, quantity</b>	1
<b>Functionality</b>	Demultiplexing   Multiplexing
<b>Interface Feature, input</b>	Standard
<b>Interface Feature, output</b>	Standard
<b>Multiplexers, quantity</b>	1
<b>Package, quantity</b>	1
<b>Port Type, optional</b>	Upgrade port

## Dimensions

<b>Depth</b>	177.80 mm   7.00 in
<b>Height</b>	71.88 mm   2.83 in
<b>Width</b>	17.27 mm   0.68 in

## Mechanical Specifications

<b>Device Type</b>	Micro VAM
<b>Access</b>	Front

## Optical Specifications

<b>Starting Wavelength</b>	1611.00 nm
----------------------------	------------

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

