



G2 Multimode OM4 Standard Module, 12 LC fibers (6 duplex ports) with internal shutters

Product Classification

Portfolio	CommScope®
Product Type	Fiber module
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OM4, LazrSPEED® 550
Total Fibers, quantity	12

Dimensions

Depth	116.84 mm 4.60 in
Height	27.94 mm 1.10 in
Width	91.44 mm 3.60 in

Environmental Specifications

Qualification Standards	TIA/EIA-568-C.3
Safety Standard	cUL UL

General Specifications

Interface, front	LC
Total Ports, quantity, front	6
Interface Feature, front	Duplex Standard
Color, front	Aqua
Adapters, quantity, front	6
Data Module Type	Standard
Intelligence Type	iPatch® ready
Interface, rear	MPO Pinned
Adapters, quantity, rear	1
Interface Feature, rear	Standard
Package Quantity	1

Optical Performance

Insertion Loss, maximum 0.47 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

