

G2 Singlemode Standard Module, 12 LC Ports with internal shutters



Product Classification

Portfolio	CommScope®
Product Type	Fiber module
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
Total Fibers, quantity	12

Dimensions

Depth	116.84 mm 4.60 in
Height	27.94 mm 1.10 in
Width	91.44 mm 3.60 in

Environmental Specifications

Qualification Standards	TIA/EIA-568-C.3
Safety Standard	cUL UL

General Specifications

Interface, front	LC
Total Ports, quantity, front	12
Interface Feature, front	Standard
Color, front	Blue
Interface, rear	MPO Pinned
Adapters, quantity, rear	1
Interface Feature, rear	Standard
Package Quantity	1

Optical Performance

Insertion Loss, maximum	1.05 dB
--------------------------------	---------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system

