

G2 Multimode OM5 WideBand Module, 12 LC Ports with internal shutters



- LazrSPEED® WideBand extends the capability of OM4 across enough spectrum to support at least four low-cost wavelengths

Product Classification

Portfolio	CommScope®
Product Type	Fiber module
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OM5, LazrSPEED® wideband
Total Fibers, quantity	12

Dimensions

Depth	116.84 mm 4.60 in
Height	27.94 mm 1.10 in
Width	91.44 mm 3.60 in

Environmental Specifications

Qualification Standards	TIA/EIA-568-C.3
Safety Standard	cUL UL

General Specifications

Interface, front	LC
Total Ports, quantity, front	12
Interface Feature, front	Standard
Color, front	Lime green
Interface, rear	MPO Pinned
Adapters, quantity, rear	1
Interface Feature, rear	Standard
Color, rear	Lime green
Package Quantity	1

Optical Performance

Insertion Loss, maximum	0.47 dB
--------------------------------	---------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system



Included Products

CS-5G-MP (Product Component—not orderable) — LazrSPEED® OM5 WideBand Multimode Fiber