

G2 4x6 Singlemode Conversion Module, 6 MPO male ports



Product Classification

Portfolio	CommScope®
Product Type	Fiber module
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
Total Fibers, quantity	24

Dimensions

Depth	109.22 mm 4.30 in
Height	27.94 mm 1.10 in
Width	91.44 mm 3.60 in

Environmental Specifications

Safety Standard	UL
------------------------	----

General Specifications

Interface, front	MPO Male
Total Ports, quantity, front	6
Interface Feature, front	Standard
Color, front	Blue
Adapters, quantity, front	6
Color, housing	Black
Data Module Type	Standard
Shuttered	No
Interface, rear	MPO Male
Adapters, quantity, rear	4
Interface Feature, rear	Reduced footprint
Color, rear	Blue
Package Quantity	1

Optical Performance

Insertion Loss, maximum 1.34 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

