



RJ45 Patch Panel, SL Series, S/STP, 24-port, black, unloaded

## Product Classification

|                              |                  |
|------------------------------|------------------|
| <b>Portfolio</b>             | NETCONNECT®      |
| <b>Product Series</b>        | SL Series        |
| <b>Product Type</b>          | RJ45 patch panel |
| <b>Regional Availability</b> | EMEA             |

## Dimensions

|               |                      |
|---------------|----------------------|
| <b>Height</b> | 44.45 mm   1.75 in   |
| <b>Width</b>  | 482.60 mm   19.00 in |

## Environmental Specifications

**Operating Temperature** -25 °C to +50 °C (-13 °F to +122 °F)

## General Specifications

|                              |                                |
|------------------------------|--------------------------------|
| <b>Total Ports, quantity</b> | 24                             |
| <b>Cable Type</b>            | Shielded                       |
| <b>Application</b>           | For use with SL Series outlets |
| <b>Color</b>                 | Black                          |
| <b>Growth Configuration</b>  | Unloaded                       |
| <b>Interface, front</b>      | RJ45 jack                      |
| <b>Package Quantity</b>      | 1                              |
| <b>Packaging Type</b>        | Bag   Box                      |
| <b>Rack Type</b>             | EIA 19 in                      |
| <b>Rack Units</b>            | 1.0                            |

## Mechanical Specifications

|                         |   |
|-------------------------|---|
| <b>Panel Style</b>      | Straight  |
| <b>Material Type</b>    | High-impact, flame retardant, thermoplastic   Steel |
| <b>Panel Mounting</b>   | Flush   |
| <b>Termination Type</b> | IDC   |

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

