

OM4 Splicing cassette, 12LC , 900µm



Product Classification

| | |
|------------------------------|---------------------------------------------------------------------|
| Portfolio | CommScope® |
| Brand | LazrSPEED® |
| Product Type | Fiber cassette with pigtails |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |

Construction Materials

| | |
|-------------------------------|---------------------|
| Fiber Type | OM4, LazrSPEED® 550 |
| Fiber Mode | Multimode |
| Total Fibers, quantity | 12 |

Dimensions

| | |
|-----------------------|---------------------|
| Depth | 165.35 mm 6.51 in |
| Height | 28.96 mm 1.14 in |
| Pigtail Length | 1.5 m 4.9 ft |
| Width | 104.65 mm 4.12 in |

Environmental Specifications

| | |
|------------------------|----|
| Safety Standard | UL |
|------------------------|----|

General Specifications

| | |
|-------------------------------------|----------|
| Interface, front | LC |
| Adapter Color | Aqua |
| Interface Feature, front | Standard |
| Package Quantity | 1 |
| Total Ports, quantity, front | 6 |

Optical Performance

| | |
|--------------------------------|---------|
| Insertion Loss, typical | 0.30 dB |
| Return Loss, minimum | 25.0 dB |

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system

