

TeraSPEED® Splicing cassette, 12LC , 900µm



Product Classification

Portfolio	CommScope®
Brand	TeraSPEED®
Product Type	Fiber cassette with pigtails
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® OS2
Total Fibers, quantity	12

Dimensions

Depth	165.35 mm 6.51 in
Height	28.96 mm 1.14 in
Pigtail Length	1.5 m 4.9 ft
Width	104.65 mm 4.12 in

Environmental Specifications

Safety Standard	UL
------------------------	----

General Specifications

Interface, front	LC
Adapter Color	Blue
Interface Feature, front	Standard
Package Quantity	1
Total Ports, quantity, front	6

Optical Performance

Insertion Loss, typical	0.25 dB
Return Loss, minimum	55.0 dB

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

RoHS 2011/65/EU
ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

