

TeraSPEED® Splicing cassette, 24LC , 900µm



## Product Classification

<b>Portfolio</b>	CommScope®
<b>Brand</b>	TeraSPEED®
<b>Product Type</b>	Fiber cassette with pigtails
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Construction Materials

<b>Fiber Type</b>	G.652.D and G.657.A1 , TeraSPEED®   OS2
<b>Total Fibers, quantity</b>	24

## Dimensions

<b>Depth</b>	165.35 mm   6.51 in
<b>Height</b>	28.96 mm   1.14 in
<b>Pigtail Length</b>	1.5 m   4.9 ft
<b>Width</b>	104.65 mm   4.12 in

## Environmental Specifications

<b>Safety Standard</b>	UL
------------------------	----

## General Specifications

<b>Interface, front</b>	LC
<b>Adapter Color</b>	Blue
<b>Interface Feature, front</b>	Standard
<b>Package Quantity</b>	1
<b>Total Ports, quantity, front</b>	12

## Optical Performance

<b>Insertion Loss, typical</b>	0.25 dB
<b>Return Loss, minimum</b>	55.0 dB

## Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

RoHS 2011/65/EU  
ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

